

#### 15 mm Microvalves

- Flow rate max 38 NI/min
- ISO 15218 interface
- 2/2-3/2 versions normally open (NO) and normally closed (NC)
- Interchangeable coil 90° orientation
- Single and multiple sub-bases single and multipolar electric connection



# **TECHNICAL CHARACTERISTICS**

Ambient temperature	-5 ÷ +50 °C					
<u> </u>	0 : 100 0					
Fluid temperature	max +50 °C					
Fluid	10 µm filtered air, lubricated or not					
Commutation system	poppet					
Ways/Positions	2/2 NC, 3/2 NC, 2/2 NO, 3/2 NO					
Pressure	max 9 bar					
Control	electric					
Return	mechanical spring					
Connections	ISO 15218 interface					
Nominal Ø	1,2 1,5					
Nominal flow rate	26 38					
Max frequency	2700 cycles/min					


# **CONSTRUCTIVE CHARACTERISTICS**

Valve body	technopolymer (aluminium external cover)
Seals	nitrile rubber
Components	stainless steel, brass

# **ELECTRIC** CHARACTERISTICS

Coil	U05 DD series
Power consumption	24 V AC - 48 V AC - 110 V AC - 230 V AC
Electrical connection	15 mm connector - Molex-type bipolar connector or loose wires
Voltage	12 V DC - 24 V DC
Manual override	with button with tool
	(upon request other manual overrides, see page 1_5)
Protection degree with con	nector IP65

# ISO 15218 Substructure



#### A Pitch

#### 3/2 NC

1 = Supply port

2 = Use

3 = Exhaust

3/2 NO 2/2 NO 1 = Exhaust 1 = Exhaust 3 = Supply port

2 = Use3 = Supply port

Drilling jig to assemble the valve on a smooth surface with a sealing plate in between. Part no. A-299-11.



#### 15 mm Microvalves



A Manual override

B Possible rotation by 180°
3/2 NC 3/2 NO

3/2 NC 1 = Supply port 2 = Use

2/2 NC

2/2 NO


3/2 NC

3/2 NO

1 = Exhaust 2 = Use 2/2 NO 1 = Exhaust 3 = Supply port 5.5

3 = Exhaust 3 = Supply port

#### Microvalves Ø 1,2 for direct current coils 2 W



**DD-051L030** 24 V DC **-** 2 W

В

Symbol	Pressure bar	Ø mm	Flow rate NI/min.	Current	Time En.	s (ms) De-en.	Weight (b) Kg	Part no.
2 ± w	0÷9	1,2	26	DC	11	11	0,018 (0,037)	A-141N
## 2 WW	0÷9	1,2	26	DC	11	11	0,018 (0,037)	A-161N
2 W 3 1	0÷9	1,2	26	DC	11	11	0,018 (0,037)	A-101N
2 www.	0÷9	1,2	26	DC	11	11	0,018 (0,037)	A-121N

Upon request 12 V DC

Coil with flying cables

#### Microvalves Ø 1,5 for direct current coils 2,5 W

	Symbol	Pressure	Ø	Flow rate	Current	Time	s (ms)	Weight(b)	Part no.
		bar	mm	NI/min.		En.	De-en.	Kg	
2/2 NC	2 1 1	0÷8	1,5	38	DC	11	11	0,018 (0,037)	A-142N
2/2 NO	2 www.	0÷8	1,5	38	DC	11	11	0,018 (0,037)	A-162N
3/2 NC	2 T 3 1	0÷8	1,5	38	DC	11	11	0,018 (0,037)	A-102N
3/2 NO	2 w	0÷8	1,5	38	DC	11	11	0,018 (0,037)	A-122N

Suggested coils	Suggested coils						
DD-052	Coil						
24 V DC - 2,5 W	with Faston						
<b>DD-052L030</b> 24 V DC - 2,5 W	Coil with flying cables						

Upon request 12 V DC

#### Microvalves Ø 1,2 for direct or alternate current

	Symbol	Pressure	Ø	Flow rate	Current	Time	s (ms)	Weight (b)	Part no.
		bar	mm	NI/min.		En.	De-en.	Kg	
2/2 NC	2 ± w	0÷9	1,2	26	DC/AC	11	11	0,018 (0,037)	A-151N
2/2 NO	2 1 3 W	0÷9	1,2	26	DC/AC	11	11	0,018 (0,037)	A-171N
3/2 NC	2 V V V V V V V V V V V V V V V V V V V	0÷9	1,2	26	DC/AC	11	11	0,018 (0,037)	A-111N
3/2 NO	2 W	0÷9	1,2	26	DC/AC	11	11	0,018 (0,037)	A-131N

Suggested coils	
DD-040 24 V AC - 50/60 Hz - 2 VA DD-050 48 V AC - 50/60 Hz - 2 VA DD-051 24 V DC - 2 W DD-070 230 V AC - 50/60 Hz - 2 VA	Coil with Faston
<b>DD-051L030</b> 24 V DC - 2 W	Coil with flying cables

Upon request 12 V DC

(b) = the weight in brackets refers to coil with faston

For technical data of coils see "Accessories>Coils"

Pilots are supplied without coil, connector and sealing plate

# Microvalves Ø 1,5 for direct or alternate current

2/2 NC 3/2 NC

Symbol	Pressure	Ø	Flow rate	Current	Time	s (ms)	Weight (b)	Part no.
	bar	mm	NI/min.		En.	De-en.	Kg	
2 1 W	0÷9	1,5	38	DC/AC	11	11	0,018 (0,037)	A-152N
2 1 3 W	0÷9	1,5	38	DC/AC	11	11	0,018 (0,037)	A-112N

Suggested coils							
<b>DD-011</b> 24 V AC - 50/60 Hz	Coil with Faston						
<b>DD-013</b> 220 V AC - 50/60 Hz - 3,5 VA <b>DD-040</b>							
24 V AC - 50/60 Hz - 3,5 VA DD-052							
24 V DC - 2,5 W <b>DD-060</b> 48 VAC - 50/60 Hz - 3,5 VA							
<b>DD-052L030</b> 24 V DC - 2,5 W	Coil with flying cables						

Upon request 12 V DC

# >> Coils





U5 flying cables weight: 0,019 Kg DD-051L030 DD-052L030

Weight: 0,019 Kg
DD-011 DD-051
DD-013 DD-052
DD-040 DD-060
DD-041 DD-070
DD-050

#### Standard manual override

Standard mandar overnac									
Operation		Notes	Symbol						
1 = with button with tool,	1 position (standard)	metallic	$\rightarrow$						
2 = with button, 1-2 posit	ions (upon request)	technopolymer red colour	$\Theta$						
<b>3</b> = with front button, 1 pe	osition (upon request)	technopolymer red colour	$\rightarrow$						
<b>4</b> = with button, 1 position	n (upon request)	metallic	$\rightarrow$						
	→ <b>&gt;</b>		→						
1	2	3	4						

 $\label{eq:bound} \textbf{(b)} = \textbf{the weight in brackets refers to coil with faston}$ 

For technical data of coils see "Accessories>Coils"
Pilots are supplied without coil, connector and sealing plate



#### Sub-base for external electric connection


Sub-base in extruded anodized aluminium with conveyed supplies and exhausts for assembling NC or NO valves. If NC and NO valves are assembled on just one base, it is necessary to insert the inverter part A-350 for NO valves.

A - 326A - \_\_\_(b) G1/8 threaded connections (standard)

A - 326B - \_ \_ (b) M5 threaded connections (upon request)


A - 326C - \_ \_\_(b) push-in connections tube 3 (upon request)


A - 326D - \_\_\_(b) push-in connections tube 4 (upon request)



#### Sub-base for integrated electric connection


Sub-base with sub-D connector in extruded anodized aluminium up to max. 13 stations with connector 15 pin (upon request up to 23 with connector 25 pin) and G1/8 threaded standard connections, with conveyed supplies and exhausts for assembling NC or NO valves with integrated coil connection and optical indication of the valve activation. If both, NO and NC valves, are assembled on just one sub-base, NC valves are always mounted on the connector side and afterwards the NO valves. The invert (part no. A-350) is inserted for NO valves.







A-301




#### Sealing plate


It blocks the seal in place when the valve is mounted on a smooth surface without a seal housing material: aluminium weight: 0,003 Kg


#### Blank plate

Unused valve stations must be closed with the blanking plate material: aluminium weight: 0,002 Kg

#### A-305








#### A-350





#### Single base material: zamak

connection: M5 weight: 0,012 Kg

#### Inverter

NO and NC valves can be mounted on a single block inserting this device between the NO valve and the sub-base. If all are NO valves, just invert air supply, without using the inverter. material: plastic weight: 0,002 Kg